

# N7 iTECH M2, M5

oświetlenie antypaniczne  
anti-panic lighting

Wymiary [mm]  
Dimensions [mm]



Montaż  
Mounting

Akcesoria  
Accessories


19,5 x 20 x 7 [cm]




Ilość opakowań:  
quantity of boxes:  
400 szt./pcs

## iTECH M2





## ZASTOSOWANIE iTECH M2, M5, S1, S2 THE USE OF RINO M2, M5, S1, S2



Wysokość montażu h (m) Mounting height h (m)	Maks. dystans ściana/oprawa [m] Max. distance wall/ fitting [m]			Maks. dystans oprawa/oprawa [m] Max. distance fitting/fitting [m]			Maks. dystans oprawa/oprawa [m] Max. distance fitting/fitting [m]			Maks. dystans oprawa/ściana [m] Max. distance fitting/wall [m]		
												
	1 h	3 h	CB	1 h	3 h	CB	1 h	3 h	CB	1 h	3 h	CB
2.5	3.8	3.8	3.8	9.6	9.6	9.6	9.6	9.6	9.6	3.8	3.8	3.8
3.0	4.0	4.0	4.0	10.4	10.4	10.4	10.4	10.4	10.4	4.0	4.0	4.0
4.0	4.2	4.2	4.2	11.7	11.7	11.7	11.7	11.7	11.7	4.2	4.2	4.2
5.0	4.5	4.5	4.5	12.7	12.7	12.7	12.7	12.7	12.7	4.5	4.5	4.5
6.0	4.7	4.7	4.7	13.5	13.5	13.5	13.5	13.5	13.5	4.7	4.7	4.7
7.0	4.7	4.7	4.7	14.0	14.0	14.0	14.0	14.0	14.0	4.7	4.7	4.7
8.0	4.5	4.5	4.5	14.5	14.5	14.5	14.5	14.5	14.5	4.5	4.5	4.5
9.0	4.5	4.5	4.5	14.3	14.3	14.3	14.3	14.3	14.3	4.5	4.5	4.5
10.0	4.0	4.0	4.0	14.9	14.9	14.9	14.9	14.9	14.9	4.0	4.0	4.0

## iTECH M5



Wysokość montażu h (m) Mounting height h (m)	Maks. dystans ściana/oprawa [m] Max. distance wall/ fitting [m]			Maks. dystans oprawa/oprawa [m] Max. distance fitting/fitting [m]			Maks. dystans oprawa/oprawa [m] Max. distance fitting/fitting [m]			Maks. dystans oprawa/ściana [m] Max. distance fitting/wall [m]		
	1 h	3 h	CB	1 h	3 h	CB	1 h	3 h	CB	1 h	3 h	CB
2,5	4,6	4,6	4,6	11,2	11,2	11,2	11,2	11,2	11,2	4,6	4,6	4,6
3,0	5,1	5,1	5,1	12,5	12,5	12,5	12,5	12,5	12,5	5,1	5,1	5,1
4,0	5,7	5,7	5,7	13,9	13,9	13,9	13,9	13,9	13,9	5,7	5,7	5,7
5,0	5,9	5,9	5,9	15,4	15,4	15,4	15,4	15,4	15,4	5,9	5,9	5,9
6,0	6,6	6,6	6,6	16,2	16,2	16,2	16,2	16,2	16,2	6,6	6,6	6,6
7,0	6,7	6,7	6,7	17,4	17,4	17,4	17,4	17,4	17,4	6,7	6,7	6,7
8,0	6,5	6,5	6,5	18,2	18,2	18,2	18,2	18,2	18,2	6,5	6,5	6,5
9,0	6,4	6,4	6,4	19,5	19,5	19,5	19,5	19,5	19,5	6,4	6,4	6,4
10,0	6,4	6,4	6,4	19,9	19,9	19,9	19,9	19,9	19,9	6,4	6,4	6,4

Typ Type	Model Model	Źródło światła Light source	Czas Time	Tryb pracy Mode	Strumień w pracy dziennej luminous flux in day mode	Strumień w pracy awaryjnej luminous flux in non-maintained mode
ST – TEST RĘCZNY / MANUAL TEST [S]						
iTECH	M2 302 ST	2W / 1xLED	3h	M/NM	115 lm	245 lm
iTECH	M2 102 COLD ST	2W / 1xLED	1h	M/NM	115 lm	245 lm
iTECH	M2 302 COLD ST	2W / 1xLED	3h	M/NM	115 lm	245 lm
iTECH	M5 105 ST	5W / 2xLED	1h	M/NM	223 lm	475 lm
iTECH	M5 305 ST	5W / 2xLED	3h	M/NM	223 lm	475 lm
iTECH	M5 105 COLD ST	5W / 2xLED	1h	M/NM	223 lm	475 lm
AT – TEST AUTOMATYCZNY / SELFTEST (AUTOTEST) [P]						
iTECH	M2 302 AT	2W / 1xLED	3h	M/NM	115 lm	245 lm
iTECH	M2 102 COLD AT	2W / 1xLED	1h	M/NM	115 lm	245 lm
iTECH	M2 302 COLD AT	2W / 1xLED	3h	M/NM	115 lm	245 lm
iTECH	M5 105 AT	5W / 2xLED	1h	M/NM	223 lm	475 lm
iTECH	M5 305 AT	5W / 2xLED	3h	M/NM	223 lm	475 lm
iTECH	M5 105 COLD AT	5W / 2xLED	1h	M/NM	223 lm	475 lm
DATA – TEST CENTRALNY AUTOMATYCZNY (MONITORING) / AUTOMATIC CENTRAL TEST (MONITORING) [ER or PRN]						
iTECH	M2 302 DATA (DATA 2)	2W / 1xLED	3h	M/NM	115 lm	245 lm
iTECH	M2 102 COLD DATA (DATA 2)	2W / 1xLED	1h	M/NM	115 lm	245 lm
iTECH	M2 302 COLD DATA (DATA 2)	2W / 1xLED	3h	M/NM	115 lm	245 lm
iTECH	M5 105 ST DATA (DATA 2)	5W / 2xLED	1h	M/NM	223 lm	475 lm
iTECH	M5 305 ST DATA (DATA 2)	5W / 2xLED	3h	M/NM	223 lm	475 lm
iTECH	M5 105 COLD DATA (DATA 2)	5W / 2xLED	1h	M/NM	223 lm	475 lm
CB – CENTRALNA BATERIA / CENTRAL BATTERY [ER or PRN]						
iTECH	M2 02 CBm	2W / 1xLED	–	–	245 lm	245 lm
iTECH	M5 05 CBm	5W / 2xLED	–	–	475 lm	475 lm

NM – praca awaryjna / non maintained  
M – praca sieciowo-awaryjna / maintained